

# Adjustable Depth 4 Post Rack System

## specifications

The adjustable depth 4 post rack shall meet EIA/ECA-310-E standards, be 45 or 52 RU, constructed of steel and capable of accepting 19" wide EIA equipment. The rack shall have adjustable depth from 23" to 42" in 0.5" increments. The equipment mounting rails shall be #12-24 threaded or cage nut square opening style mounting. The equipment mounting rails shall include printed rack unit numbering from bottom up. The rack shall accept shelve units and equipment brackets. The front and rear structural posts of the rack shall be capable of mounting NetRunner™ or PatchRunner™ 2 Vertical Cable Managers and accessories such as power distribution units, waterfalls and vertical tie-off brackets. The construction method shall ensure an electrically bonded structure for ease of grounding. The rack shall contain eight masked grounding locations for ease of selection for lug connection position.



## technical information

Part Number	RU	Height In. (mm)	Width In. (mm)	Depth In. (mm)
AR4P(WH)	45	84.13 (2136.9)	20.31 (515.9)	23.00 to 42.00 (584.2 to 1066.8)
R4PCN(WH)	45	84.13 (2136.9)	20.31 (515.9)	23.00 to 42.00 (584.2 to 1066.8)
AR4P96(WH)	52	96.13 (2441.7)	20.31 (515.9)	23.00 to 42.00 (584.2 to 1066.8)
AR4PCN96(WH)	52	96.13 (2441.7)	20.31 (515.9)	23.00 to 42.00 (584.2 to 1066.8)

## key features and benefits

<b>Adjustable depth</b>	Supports equipment mounting depths from 23" to 42" in 0.5" increments to provide greater flexibility with a single part number
<b>Welded steel construction</b>	UL listed, 2000 lbs. load capacity provides greater stability
<b>Self-squaring</b>	Front-to-back braces are installed in two axes, helping to maintain squareness of the rack during assembly
<b>Inward facing feet</b>	Reduces overall front-to-back footprint, aligning better to floor tiles
<b>Color options</b>	Available in Black and White
<b>Numerical rack unit identification</b>	Allows for quick location of rack spaces speeding installation of rack mount items, racks are numbered from bottom up
<b>Fully bonded structure</b>	Paint piercing hardware electrically bonds the rack when assembled, eliminating the need for additional bonding components
<b>PEM stud and carriage bolt construction</b>	Eliminates the need for a second wrench, increasing speed and ease of assembly
<b>Multiple options for mounting accessories</b>	Accessories such as PDU brackets, vertical tie-off brackets, waterfalls mount on posts or front-to-back braces for greater application flexibility
<b>Integrated masked grounding locations</b>	Eight masked grounding locations available for optimal lug connection position
<b>7 foot and 8 foot versions</b>	Allows maximum utilization of available vertical space

## applications

The Panduit Adjustable Depth 4 Post Rack System is designed to support network equipment found in data center, telecommunication room and lab environments. The rack combines the stability of a cabinet with the accessibility of an open rack to provide the user with maximum flexibility when designing the network layout. Front and rear weldments with adjustable front-to-back

braces provide the required strength and flexibility needed to work with various types of active equipment. The open design allows for maximum airflow in and around the rack. The Adjustable Depth 4 Post Rack System is part of a complete rack and cable management system that manages, protects, and showcases your network investment.

### Adjustable Depth 4 Post Racks 7 foot and 8 foot

23" – 42" depth	
#12-24 threaded rails:	AR4P <sup>^</sup>
Cage nut rails:	AR4PCN <sup>^</sup>

### 4 Post Racks Accessories

Vertical tie-off bracket:	V4PTOB <sup>^</sup>
Vertical PDU mounting brackets:	CVPDUB <sup>^</sup>
Top trough for use with PatchRunner™ 2:	PR2VWF <sup>^</sup>
Top trough for use with PatchRunner™ 2 Enhanced:	PE2VWF <sup>^</sup>
Shelves	
19"W x 30"D:	RSHLF <sup>^</sup>
19"W x 23"D:	RSHLF23
19"W x 36"D:	RSHLF36 <sup>^</sup>
Rack anchor kit for concrete floor:	RFAKIT
Rack anchor kit for raised floor:	RFA3KIT
100 cage nuts w/ M6 screws:	CNWSM6-C
100 cage nuts w/ #12-24 screws:	CNWS1224-C
100 #12-24 screws:	S1224-C
Fiber Storage Ring:	WMFS24

### PatchRunner™ 2 Vertical Cable Managers with Doors – 7 foot and 8 foot

6" W, front and rear:	PR2VD06 <sup>^</sup>
6" W, front only:	PR2VFD06 <sup>^</sup>
8" W, front and rear:	PR2VD08 <sup>^</sup>
8" W, front only:	PR2VFD08 <sup>^</sup>
10" W, front and rear:	PR2VD10 <sup>^</sup>
10" W, front only:	PR2VFD10 <sup>^</sup>
12" W, front and rear:	PR2VD12 <sup>^</sup>
12" W, front only:	PR2VFD12 <sup>^</sup>


### NetRunner™ Vertical Cable Managers 7 foot

4.9" wide front and rear:	WMPV45E
4.9" wide front only:	WMPVF45E
6.7" wide front and rear:	WMPVHC45E
6.7" wide front only:	WMPVHCF45E

<sup>^</sup>For part numbers 8 feet tall, add "96" to end of part number. Ex: AR4P96 or AR4PCN96

<sup>^</sup>For white product, add "WH" to end of part number. Ex: AR4PWH or AR4PCN96WH

# Adjustable 4 Post Rack System



- |  |   |
|--|---|
| <p><b>1</b> AR4P* – 4 Post Rack<br/>#12-24 threaded rails<br/>84.0"H x 20.3"W x 23" to 42"D, 45 rack units (RU)</p> <p>AR4PCN* – 4 Post Rack<br/>cage nut rails<br/>84.0"H x 20.3"W x 23" to 42"D, 45 RU (not shown)</p> | <p><b>5</b> RSHLF – 4 Post Rack Shelf<br/>19"W x 30"D</p> <p>RSHLF23 – 4 Post Rack Shelf<br/>19"W x 23"D (not shown)</p> <p>RSHLF36 – 4 Post Rack Shelf<br/>19"W x 36"D (not shown)</p>   |
| <p><b>2 3 4</b> PatchRunner™ 2 Vertical Managers<br/>Available in 6", 8", 10", and 12"<br/>widths to fit both 7' and 8' racks</p>  | <p><b>6</b> PR2VWF – Top Trough with waterfall<br/>creates pathway above rack</p> <p><b>7</b> CVPDUB – PDU Bracket (set of 2)</p> <p><b>8</b> V4PTOB – Vertical Tie-Off Bracket creates<br/>additional pathway on rear side<br/>of rack</p> |

\*For part numbers 8 feet tall, add "96" to end of part number. Ex: AR4P96 or AR4PCN96.

## WORLDWIDE SUBSIDIARIES AND SALES OFFICES

PANDUIT US/CANADA  
Phone: 800.777.3300

PANDUIT EUROPE LTD.  
London, UK  
Phone: 44.20.8601.7200

PANDUIT SINGAPORE PTE. LTD.  
Republic of Singapore  
Phone: 65.6305.7575

PANDUIT JAPAN  
Tokyo, Japan  
Phone: 81.3.6863.6000

PANDUIT LATIN AMERICA  
Guadalajara, Mexico  
Phone: 52.33.3777.6000

PANDUIT AUSTRALIA PTY. LTD.  
Victoria, Australia  
Phone: 61.3.9794.9020

For a copy of Panduit product warranties, log on to [www.panduit.com/warranty](http://www.panduit.com/warranty)

For more information

Visit us at [www.panduit.com](http://www.panduit.com)

Contact Customer Service by email: [cs@panduit.com](mailto:cs@panduit.com)  
or by phone: 800.777.3300

**PANDUIT**™

© 2020 Panduit Corp.  
ALL RIGHTS RESERVED.  
RKSP194--WW-ENG  
9/2020