


P/N	CABLE LENGTH FT (METERS)
VS2-CABLE-02	2 (.61)
VS2-CABLE-04	4 (1.22)
VS2-CABLE-08	8 (2.44)
VS2-CABLE-16	16 (4.88)
VS2-CABLE-20	20 (7.1)
VS2-CABLE-30	30 (9.15)

NOTES:

1. READ VERISAFE 2.0 INSTRUCTION MANUAL (B21110) BEFORE USING.
2. FOR USE WITH VS2-AVT-* PART NUMBERS.
3. OPERATING TEMPERATURE: -45°C TO 60°C
4. 600V, HIGH FLEX INDUSTRIAL ETHERNET U/UPT STRANDED WIRE.
5. NOT QUALIFIED TO BE USED AS AN ETHERNET CABLE.

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
0	5/10/22	DFA	ZSG	MSAD	INITIAL RELEASE	GAECN06510

INSPECTION INSTRUCTION NUMBER TITLE		FMEA & CONTROL PLAN NUMBER	
VERISAFE 2.0 SYSTEM CABLE			
CUSTOMER DRAWING			
ITEM REVISION NAME 18I216PP/05		PANDUIT	
DATASET FILE NAME 18I216PP_DC/05			
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]		MATERIAL: N/A	
.x ± .1 [2.54]	.xxx ± .005 [.127]	DRAWING NUMBER: 18I216PP_DC	
.xx ± .01 [.25]	ANGLES ± 5 °		
 THIRD ANGLE PROJECTION		SCALE	
DRAWN BY DFA	DATE 5/10/22	CHK ZSG	SCALE NONE
SHT 1 OF 1		SIZE B	

D10100DB/17