

Panduit™ PXE Mobile Solutions deliver high quality products that help you do your job smarter, faster and easier.

These solutions combine Epson's world-class printing technology with Panduit's industry-leading performance and field-tested durability. This full line of Electrical and Network label printers provides the solution that's best for you, from on-site smaller jobs to on-demand high volume label printing projects.



FEATURES

PART NUMBER	MP75	MP100/E	MP200	MP300/E
Price	€	€€	€€	€€€
Automatic Cutter		✓	✓	✓
Half-Cut Feature			✓	✓
PC Interface and Printing for Easy-Mark Plus™ Software		✓	✓	✓
Bluetooth/Wi-Fi/Mobile App Compatible		✓		
Maximum Continuous Label Media Width	19 mm	25,4 mm	25,4 mm	38,1 mm
Print Speed	0,25 lps	0,6 lps	1,2 lps	1,4 lps
Weight	400 g	600 g	1.100 g	3.200 g
Size	112 mm W x 71 mm H x 170 mm L	60 mm W x 150 mm. H x 137 mm L	137 mm W x 89 mm H x 295 mm L	137 mm W x 97 mm H x 295 mm L
Print Resolution	180 dpi	180 dpi	180 dpi	360 dpi

LABEL TYPES

Continuous Vinyl & Polyester Tapes	✓	✓	✓	✓
Continuous Heat Shrink Tubing	✓	✓	✓	✓
Continuous Self-Laminating Labels		✓	✓	✓
Continuous Magnetic Tape		✓	✓	✓
Die-Cut Self-Laminating Labels				✓
Die-Cut Component Labels				✓
Turn-Tell™ Labels				✓

For a copy of Panduit product warranties, log on to www.panduit.com/warranty

©2022 Panduit Corp.
ALL RIGHTS RESERVED.
IDFL20--SA-ENG
10/2022

For more information, visit us at: www.panduit.com
Contact Customer Service by email: cs@panduit.com
or by phone: 800-777-3300

PANDUIT

EPSON

EXCEED YOUR VISION

PORTABLE LABEL PRINTER PARTNER