

Tilt Up Style Table Box

specifications

Panduit table boxes provide a way to have connectivity and power at a conference room table or podium. The table boxes should be able to open and close. Each table box is supplied with 1 front faceplate in both Mini-Com and NetKey footprint. The Mini-Com faceplate is compatible with any Panduit Mini-Com module. The NetKey faceplate is compatible with any Panduit NetKey module or any standard keystone module. Each table box comes prepopulated with an UL/cUL listed power receptacle with 12 AMP AC capacity. Mounting brackets, screws, wiring nuts, cable clamps, faceplates, faceplate screws and an Allen key are included with each table box. Tilt up table boxes feature a leaf spring design for lifelong usage. The tilt up feature is easily accessed with the top is pressed down and released. The unit can be hidden by pressing down until the top is level with the table, then released.



PND110

technical information

Material:	Aluminum
Power Receptacle:	UL-cUL listed power module with 12 AMP AC capacity with 9.5ft power cord
Dimensions:	4.14 in (height), 7.86 in (width), 6.53 in (depth)
Color:	Black (BL)
Minimum Table Thickness:	0.2 in (5 mm)
Maximum Table Thickness:	2.5 in (64 mm)
Operating temperature:	10 – 40 degrees C
Module Spaces:	up to 4 modules

key features and benefits

Removable Front Faceplate	Each table box is supplied with both a Mini-Com and NetKey (keystone) removable faceplate. Once installed, a faceplate can be removed and remounted for future moves, adds and changes
Leaf Spring Design	Leaf spring design will last a lifetime and will not require any maintenance
Designer profile	Table box mounts flush with surface allowing an aesthetically pleasing appearance and box can be easily closed when not in use for a clean look
Power and Data	Each box comes pre-populated with a power receptacle and has room for multiple connector styles in the removable front faceplates

applications

Panduit tilt up table boxes are ideal for conference room tables, podiums, and work table surfaces. They are a component of Panduit's end to end copper cabling and audio video system. This end-to-end system is interoperable and backwards compatible, providing design flexibility to protect A/V and network systems well into the future.

Table Boxes

Nook Style:	PND100
Tilt Up Style:	PND110
Retractable HDMI cable for Nook Style:	PND400

Mini-Com[®] Modules

Blank Module:	CMBBL-X
Cat 6 Jack:	CJ688TGBL
Cat 6A Jack:	CJ6X88TGBL
Angled Wire Caps:	CJLRCAPBU-C
2-Position HDMI Module:	CMHDMIBL
2-Position HDMI Module with Pigtail:	CMHDMITBL
USB Module:	CMUSBAABL
3.5 Stereo Coupler:	CM35MSCBLY


NetKey[®] Modules

Blank Module:	NKBMBL-X
Cat 6 Jack:	NK688MBL
Cat 6A Jack:	NK6X88MBL
HDMI Module:	NKHDMIBL
USB Module:	NKUSBAABL
3.5 Stereo Coupler:	NK35MSCBL


[^]For additional colors and module types, please see Panduit.com

Tilt Up Style Table Box


Tilt up Box



Top View



Front View



Side View

PND110

Dimensions are in inches (Dimensions in parenthesis are metric)

WORLDWIDE SUBSIDIARIES AND SALES OFFICES

PANDUIT US/CANADA
Phone: 800.777.3300

PANDUIT EUROPE LTD.
London, UK
cs-emea@panduit.com
Phone: 44.20.8601.7200

PANDUIT SINGAPORE PTE. LTD.
Republic of Singapore
cs-ap@panduit.com
Phone: 65.6305.7575

PANDUIT JAPAN
Tokyo, Japan
cs-japan@panduit.com
Phone: 81.3.6863.6000

PANDUIT LATIN AMERICA
Guadalajara, Mexico
cs-la@panduit.com
Phone: 52.33.3777.6000

PANDUIT AUSTRALIA PTY. LTD.
Victoria, Australia
cs-aus@panduit.com
Phone: 61.3.9794.9020

For a copy of Panduit product warranties, log on to www.panduit.com/warranty

For more information

Visit us at www.panduit.com

Contact Customer Service by email: cs@panduit.com
or by phone: 800.777.3300

PANDUIT[®]

©2018 Panduit Corp.
ALL RIGHTS RESERVED.
OTSP57--SA-ENG
6/2018