Terminal Block Markers

specifications

Terminal Block Markers are to be continuously molded, flexible polymer material. The elastomeric material shall readily accept continuous thermal transfer print, using the Panduit TDP43ME printer. Product shall be resistant to scratching, smearing, and rubbing. Product shall be able to be installed and removed without the use of hand tools.



Material:	Thermoplastic Elastomer (TPE)		
Operating temperature:	-40°F to 180°F (-40°C to 82°C)		
Flammability:	UL 94-V0		
Recommemded usage:	Indoor use only		
Standards compliance:	Halogen free and RoHS Meets EN 61010-1 (VDE 0411-1) for abrasion and wipe resistance Meets EN ISO 175 for oil and chemical resistance Meets EN 60464-2:2001 for resistance to solvents Meets IEC 60947-7-1/2 for resistance to aging Meets IEC 60068-2-6 for vibration resistance		

I

n

D

D

I

I

102

103

107

108

109

key features and benefits

Thermal transfer printable	Faster printing speeds					
	Use single printer for all control panel labels; terminal block markers, heat shrink, self-laminating, raised panel, arc flash labels, voltage markers, and safety labels					
	Print-on-demand using Panduit labeling software					
	Allows use of standard resin ribbon – no need for difficult, messy, or expensive ink cartridges					
Provided on a convenient continuous reel	Faster marker installation; install many markers in a single step					
	Less marker waste - print only as many as you need					
	Easy loading in Panduit TDP43ME printer and roll stand					
Durability	Flexible markers have superior holding strength in terminal blocks, eliminating markers that fall out					
	Chemical and abrasion resistant					
	Shock and vibration resistant					
	Markers have an easy pull-apart design, and can be easily replaced for any panel changes					

SPECIFICATION SHEET

Terminal Block	Markers
5mm x 12mm:	TB05X12EWT-AB1
6mm x 12mm: 8mm x 12mm:	TB06X12EWT-AB1 TB08X12EWT-AB1
5mm x 8mm:	TB05X08EWT-AB2
6mm x 8mm:	TB06X08EWT-AB2
Easy Mark [™] PL	US
Labeling Softwa	are
CD-ROM:	EMPLUS-CD
Online	
download:	EMPLUS-DL
USB floob drives	
flash drive:	EMPLUS-2GO
Server based version:	EMPLUS-SERVER
	abeling Software
CD-ROM:	PROG-CCCD
Thermal Transf	er
Desktop Printer	
Desktop Printer 300 dpi:	
300 dpi: External roll	TDP43ME
300 dpi:	TDP43ME
300 dpi: External roll	TDP43ME : TDP43ME-RS
300 dpi: External roll stand(required) Recommended TDP43ME	TDP43ME : TDP43ME-RS
300 dpi: External roll stand(required) Recommended TDP43ME black resin	TDP43ME : TDP43ME-RS Ribbon
300 dpi: External roll stand(required) Recommended TDP43ME	TDP43ME : TDP43ME-RS
300 dpi: External roll stand(required) Recommended TDP43ME black resin	TDP43ME : TDP43ME-RS Ribbon RMER1BL
300 dpi: External roll stand(required) Recommended TDP43ME black resin 1" wide: Other Compatib TDP43ME	TDP43ME : TDP43ME-RS Ribbon RMER1BL
300 dpi: External roll stand(required) Recommended TDP43ME black resin 1" wide: Other Compatik TDP43ME black resin	TDP43ME : TDP43ME-RS <i>Ribbon</i> RMER1BL
300 dpi: External roll stand(required) Recommended TDP43ME black resin 1" wide: Other Compatik TDP43ME black resin 2" wide:	TDP43ME : TDP43ME-RS Ribbon RMER1BL
300 dpi: External roll stand(required) Recommended TDP43ME black resin 1" wide: Other Compatik TDP43ME black resin 2" wide: TDP43ME	TDP43ME : TDP43ME-RS <i>Ribbon</i> RMER1BL
300 dpi: External roll stand(required) Recommended TDP43ME black resin 1" wide: Other Compatik TDP43ME black resin 2" wide: TDP43ME black resin	TDP43ME TDP43ME-RS <i>Ribbon</i> RMER1BL DIE Ribbons RMER2BL
300 dpi: External roll stand(required) Recommended TDP43ME black resin 1" wide: Other Compatik TDP43ME black resin 2" wide: TDP43ME	TDP43ME : TDP43ME-RS <i>Ribbon</i> RMER1BL

applications

Panduit computer printable terminal block markers are ideally suited for printing markers for terminal block labeling applications within industrial control panels. Panduit terminal block makers are designed from a unique material and with an innovative design that allows them to be printed

on-demand with the TDP43ME, and with a standard resin ribbon. The markers are provided on a continuous reel to allow printing of the precise quantity needed for a job. The continuous design makes printing and installing markers faster as well.

Terminal Block Markers



Create and print terminal block markers quickly using Easy-Mark[™] Plus Labeling Software.

part information



Continuous reel of markers enables fast printing and aligns easily in printer using snap-in width guides.




Print terminal block markers using TDP43ME Thermal Transfer Desktop Printer and accessory roll stand.



Durable marker design allows quick and easy installation.

Part Number	Description	Color	A Width mm	B Height mm	Markers Per Roll	Allen-Bradley Terminal Block Compatibility	Weidmuller Terminal Block Compatibility
TB05X12EWT-AB1	Flexible terminal block markers on continuous rolls	White	5.0	12.0	1000	1492-J3, 1492-W3	WDU 2.5
TB06X12EWT-AB1	Flexible terminal block markers on continuous rolls	White	6.0	12.0	1000	1492-J4, 1492-W4	WDU 4
TB08X12EWT-AB1	Flexible terminal block markers on continuous rolls	White	8.0	12.0	750	1492-J6	WDU 6
TB05X08EWT-AB2	Flexible terminal block markers on continuous rolls	White	5.0	8.0	1000	1492-JD3, 1492-L3	WDR 2.5
TB06X08EWT-AB2	Flexible terminal block markers on continuous rolls	White	6.0	8.0	1000	1492-JD4, 1492-L4	WDR 4



TDP43ME printer and accessories

Part Number	Description
TDP43ME	300 dpi printer; includes printer, Panduit [®] Easy-Mark [™] Labeling Software, RMEH4BL black hybrid ribbon, AC power adapter with US power cord, USB cable, user manual, quick start card, driver disk, and TDP43ME-TB-KIT terminal block marker adapter kit; for use in North America.
TDP43ME-RS	External label roll stand for TDP43ME printer; used to rear feed labels that are supplied on 3" cores.
TDP43ME-TB-KIT	Terminal block marker adapter kit for TDP43ME printer (included with new TDP43ME printers and available as an optional accessory for older TDP43ME printers).
RMER1BL	Ribbon, resin, 1.1" wide, 300' long, for use with TDP43ME, Black.
EMPLUS-CD	Easy-Mark [™] Plus Labeling Software – CD-ROM version.

Related Products









Voltage Markers

DISCLAIMER: The information contained herein is intended as a guide for use by persons having technical skill at their own discretion and risk. Before using, buyer shall determine the suitability of the Panduit product for his intended use and buyer assumes all risk and liability whatsoever in connection therewith.

WORLDWIDE SUBSIDIARIES AND SALES OFFICES

PANDUIT CANADA Markham, Ontario cs-cdn@panduit.com Phone: 800.777.3300 PANDUIT EUROPE LTD. I London, UK I cs-emea@panduit.com Phone: 44.20.8601.7200 I

PANDUIT SINGAPORE PTE. LTD. Republic of Singapore cs-ap@panduit.com Phone: 65.6305.7575 PANDUIT JAPAN Tokyo, Japan cs-japan@panduit.com Phone: 81.3.6863.6000

PANDUIT LATIN AMERICA Guadalajara, Mexico cs-la@panduit.com Phone: 52.33.3777.6000 PANDUIT AUSTRALIA PTY. LTD. Victoria, Australia cs-aus@panduit.com Phone: 61.3.9794.9020

For a copy of Panduit product warranties, log on to www.panduit.com/warranty

For more information

Visit us at www.panduit.com

PANDUIT®

Contact Customer Service by email: cs@panduit.com or by phone: 800.777.3300 ©2016 Panduit Corp. ALL RIGHTS RESERVED. IDSP27--WW-ENG 12/2016