PatchRunner™2 Vertical Cable Managers

specifications

The vertical cable manager shall consist of a metal backbone with cable management fingers that align with EIA rack spacing. The fingers shall be molded out of plastic and provide integral bend radius control throughout the entire length. The backbone shall have pass through holes for front to back cabling, with the option to blank off with a plug. The manager shall accept a metal, hinged, push-to-close door that can open to the right or left. The door support brackets shall be integrated into the manager with no assembly required. The manager shall accept plastic slack management spools that can be repositioned as required. The vertical panel shall be able to manage all the cable on the rack without the aid of horizontal cable managers.



key features and benefits

NEW Improved door function	"Push-to-close" door design allows for easy operation	
NEW Dual hinged doors are included	Doors ship with managers, simplifying ordering process with less packaging waste	
NEW Integrated door brackets	No brackets to install; faster installation while reducing labor cos	
NEW Color options	Managers and doors are available in black and white	
NEW High Density with increased cable capacity	Up to 17% more usable capacity over existing PRV Vertical Managers	
Curved fingers	Support cables as they transition to vertical pathway eliminating need for horizontal managers	
Individual fingers	Aligns with rack spaces to simplify cable routing changes	
Integral bend radius control	Maintains cable bend radius ensuring network performance and system reliability	
Optional snap on vertical retainers	Can be placed on fingers to help retain cables in channel for improved cable management and appearance	
Optional slack management spools	Organize and manage patch cord slack allowing for standardization of patch cord lengths	

applications

PatchRunner™2 Vertical Cable Managers are designed to manage high-density networking equipment in, up to, half the area required by traditional cable management systems. Molded cable management fingers, with integral bend radius control, combine with Panduit angled patch panels to eliminate the need for horizontal cable managers. This frees up rack space for additional patch panels, active equipment, or cable pathways reducing the

number of racks that may be required for the network layout. The reduction in square footage combined with fewer components ordered, inventoried and installed results in significant cost savings for the network infrastructure. When used with Panduit connectivity, patch cords, and racks, the user receives a complete cable management solution that maximizes density while minimizing the area required for their network.



Vertical Cable Managers w/doors - 6.5 foot				
Dual-sided with two doors:				
6" wide:	PR2VD0679			
12" wide:	PR2VD1279			
Dual-sided with one door:				
6" wide:	PR2VSD0679			
12" wide:	PR2VSD1279			
Single-sided with one door:				
6" wide:	PR2VFD0679			
12" wide:	PR2VFD1279			
Standard EIA Racks – 6.5 foot				

Otariaara Entiriadito	0.0 1000
2 post rack:	R2P79
4 post rack:	R4P79
4 post rack:	R4PCN79
Vertical Cable Manage	rs w/doors - 7 foot

Dual-sided with two doors: 6" wide: PR2VD06[^] 8" wide: PR2VD08[^] 10" wide: PR2VD10[^] 12" wide: PR2VD12[^] Dual-sided with one door: PR2VSD06^ 6" wide: 8" wide: PR2VSD08[^] 10" wide: PR2VSD10[^]

10" wide: PR2VSD10^
12" wide: PR2VSD12^
Single-sided with one door:
6" wide: PR2VFD06^
8" wide: PR2VFD08^
10" wide: PR2VFD10^
12" wide: PR2VFD12^
Vertical Cable Managers w/doors - 8 foot

6" wide: PR2VD0696^
8" wide: PR2VD0896^
10" wide: PR2VD1096^
12" wide: PR2VD1296^
Dual-sided with one door:
6" wide: PR2VSD0696^
8" wide: PR2VSD0896^
10" wide: PR2VSD1096^

Dual-sided with two doors:

12" wide: PR2VSD1296"
Single-sided with one door:

6" wide: PR2VFD0696^
8" wide: PR2VFD0896^
10" wide: PR2VFD1096^
12" wide: PR2VFD1296^
Standard EIA Racks - 7 foot

2-Post aluminum rack with
#12-24 threaded rails: R2P*^
4-Post steel rack with
#12-24 threaded rails: R4P*^
4-Post steel rack with
cage nut rails: R4PCN*^
Accessories

7" front slack PRSP7 management spool: 5" rear slack management spool: PRSP5 PR2VEP*^ End panel: Cable retainer: WR5E-X Waterfall for use with 2-post or 4-post rack and PR2V managers: PR2VWF^ Pass-through hole blanking plugs (Kit of five plugs): PR2VBPK Pass-through bend

radius grommets
(Kit of five grommets): PR2VGK
15RU finger section
replacement kit: PR2VRFK15'
6RU finger section
replacement kit: PR2VRFK6^

Rear Gate System Kits (for use with Single-sided managers)

6" wide: PR2VRGSK06 8" wide: PR2VRGSK08 9" wide: PR2VRGSK10 10" wide: PR2VRGSK12

^{*}For part numbers 8 feet tall, add "96" to end of part number. Ex: PR2VEP96 or R2P96

[^]For part numbers in white, add "WH" to end of part number. Ex: PR2VD06WH or R2PWH

PatchRunner™2 Vertical Cable Managers

technical information

6.5 Foot Managers and Doors

Part Number	RU	Height in (mm)	Width in (mm)	Depth in (mm)
Dual Sided				
PR2VD0679	42	78.9 (2003)	6.0 (152)	20.7 (526)
PR2VD1279	42	78.9 (2003)	12.0 (305)	20.7 (526)
Single Sided				
Single Sided PR2VFD0679	42	78.9 (2003)	6.0 (152)	12.0 (305)
	42 42	· ,	6.0 (152) 12.0 (305)	12.0 (305) 12.0 (305)

7 Foot Managers and Doors

Part Number	RU	Height in (mm)	Width in (mm)	Depth in (mm)
Dual Sided				
PR2VD06*	45	83.9 (2130)	6.0 (152)	20.7 (526)
PR2VD08*	45	83.9 (2130)	8.0 (203)	20.7 (526)
PR2VD10*	45	83.9 (2130)	10.0 (254)	20.7 (526)
PR2VD12*	45	83.9 (2130)	12.0 (305)	20.7 (526)
Single Sided				
PR2VFD06*	45	83.9 (2130)	6.0 (152)	12.0 (305)
PR2VFD08*	45	83.9 (2130)	8.0 (203)	12.0 (305)
PR2VFD10*	45	83.9 (2130)	10.0 (254)	12.0 (305)
PR2VFD12*	45	83.9 (2130)	12.0 (305)	12.0 (305)

Add "WH" to end of part numbers for white products

8 Foot Managers and Doors

Part Number	RU	Height in (mm)	Width in (mm)	Depth in (mm)	
Dual Sided					
PR2VD0696*	52	95.9 (2435)	6.0 (152)	20.7 (526)	
PR2VD0896*	52	95.9 (2435)	8.0 (203)	20.7 (526)	
PR2VD1096*	52	95.9 (2435)	10.0 (254)	20.7 (526)	
PR2VD1296*	52	95.9 (2435)	12.0 (305)	20.7 (526)	
Single Sided					
PR2VFD0696*	52	95.9 (2435)	6.0 (152)	12.0 (305)	
PR2VFD0896*	52	95.9 (2435)	8.0 (203)	12.0 (305)	
PR2VFD1096*	52	95.9 (2435)	10.0 (254)	12.0 (305)	
PR2VFD1296*	52	95.9 (2435)	12.0 (305)	12.0 (305)	

^{*} Add "WH" to end of part numbers for white products

1.R2P - 19" Standard EIA Rack 19" x 7", 45 RU

PatchRunner™2 Vertical Cable Managers and Doors


2a. PR2VD06 - 6" wide 2b. PR2VD08 - 8" wide

2c. PR2VD12 - 12" wide

Angled Modular Patch Panels 3a. CPPLA48WBLY - 2 RU, 48-Port 3b. CPPA48HDWBLY - 1 RU, High Density 48 - Port

Cable Management Accessories 4.NM4 - Cable Manager, 4 RU 5.CMT4 - Trough, 4 RU

6.PR2VEP - End Panel 7.PR2VWF - Waterfall



WORLDWIDE SUBSIDIARIES AND SALES OFFICES

PANDUIT US/CANADA Phone: 800.777.3300

PANDUIT EUROPE LTD. London, UK Phone: 44.20.8601.7200

PANDUIT SINGAPORE PTE. LTD. Republic of Singapore Phone: 65.6305.7575

PANDUIT JAPAN Tokyo, Japan Phone: 81.3.6863.6000 PANDUIT LATIN AMERICA Guadalajara, Mexico Phone: 52.33.3777.6000

PANDUIT AUSTRALIA PTY. LTD. Victoria, Australia Phone: 61.3.9794.9020

For a copy of Panduit product warranties, log on to www.panduit.com/warranty



Contact Customer Service by email: cs@panduit.com or by phone: 800.777.3300

7/2019

