



## General Purpose Contractor Cable Ties

- -40° to 85°C Operating Temp.
- UL Listed
- Plenum Rated AH-2 for indoor use
- Black UV Weather resistant nylon material for outdoor use
- Halogen Free Polyamide 6.6

Standard Part Number		Bulk Part Number		Length (In.)	Max. Bundle Dia. (In.)	Width (in.)	Min. Loop Tensile Strength (Lbs.)	Length (mm)	Max. Bundle Dia. (mm)	Width (mm)	Min. Loop Tensile Strength (N)	Std. Pkg. Qty.	Bulk Pkg. Qty.
Natural Nylon 6.6 (Indoor Use)	UV Weather Resistant Nylon 6.6 (Outdoor Use)	Natural Nylon 6.6 (Indoor Use)	UV Weather Resistant Nylon 6.6 (Outdoor Use)										
S4-18-C	S4-18-C0	S4-18-M	S4-18-M0	3.94	0.87	0.10	18	100	22	2.5	80	100	1000
S5-50-C	S5-50-C0	S5-50-M	-	4.70	0.94	0.19	50	120	24	4.8	222	100	1000
S6-40-C	S6-40-C0	S6-40-M	S6-40-M0	5.51	1.30	0.14	40	140	33	3.6	178	100	1000
S6-50-C	S6-50-C0	S6-50-M	S6-50-M0	6.30	1.50	0.19	50	160	38	4.8	222	100	1000
S7-50-C	S7-50-C0	S7-50-M	S7-50-M0	7.40	1.81	0.19	50	188	46	4.8	222	100	1000
S8-18-C	S8-18-C0	-	-	7.87	2.09	0.10	18	200	53	2.5	80	100	1000
S8-40-C	S8-40-C0	-	S8-40-M0	7.87	2.09	0.14	40	200	53	3.6	178	100	1000
S8-50-C	S8-50-C0	-	S8-50-M0	8.46	2.09	0.19	50	215	53	4.8	222	100	1000
S10-50-C	S10-50-C0	-	-	9.84	2.36	0.19	50	250	60	4.8	222	100	-
S12-40-C	S12-40-C0	-	S12-40-M0	11.81	2.99	0.14	40	300	76	3.6	178	100	1000
S12-50-C	S12-50-C0	S12-50-M	S12-50-M0	11.81	2.99	0.19	50	300	76	4.8	222	100	1000
S14-120-L	S14-120-L0	S14-120-TL	S14-120-TL0	14.49	4.02	0.30	120	368	102	7.6	534	50	250
-	S15-40-C0	-	-	14.57	4.02	0.14	40	370	102	3.6	178	100	-
S15-50-C	S15-50-C0	S15-50-M	S15-50-M0	14.57	4.02	0.19	50	370	102	4.8	222	100	1000
S17-50-C	S17-50-C0	S17-50-M	-	16.93	4.33	0.19	50	430	110	4.8	222	100	1000
S18-175-L	S18-175-L0	-	-	17.71	5.20	0.35	175	450	132	9.0	0	50	-
S21-175-L	-	S21-175-C	S21-175-C0	20.71	5.51	0.35	175	530	140	9.0	778	50	100
S21-50-C	S21-50-C0	S21-50-M	S21-50-M0	20.87	5.51	0.19	50	530	140	4.8	222	100	1000
S21-120-L	S21-120-L0	S21-120-C	S21-120-C0	20.98	5.51	0.30	120	533	140	7.6	534	50	100
-	S24-175-L0	-	-	24.02	7.36	0.35	175	610	187	9.0	778	50	-
-	S31-175-L0	-	-	30.55	8.98	0.35	175	776	228	9.0	778	50	-
-	S36-175-L0	-	-	35.91	10.35	0.35	175	920	263	9.0	778	50	-
-	S48-175-L0	-	-	48.03	14.37	0.35	175	1220	365	9.0	778	50	-