


Control Panel Cable Management, Space Savings, Noise Reduction, Grounding/Bonding, Identification, Networking, Power and Safety



\* Other Panduit products shown but not called out include duct, lugs, terminals, ferrules, labels, cable ties, mounts, overhead cable tray and more

- Use this drawing when:
- Designing a new control panel
  - Retro-fitting an existing panel
  - Addressing performance or reliability issues
  - Running out of panel space
  - Protecting equipment and people

## Bill of Materials

Part Number	Description
<b>Cable Protection, Connector and Management</b>	
CPM122S-C	Control panel switch cable tie mount
FL12X12LG-A	Slotted sidewall, open finger flexible wiring duct
ARC.68-A-C	Adjustable and releasable clamp
ABDCM30-A-C	Dynamic cable manager for panel strain relief
PW38F-TL	3/8" Pan-Wrap split harness wrap
IAEBH6	Category 6, RJ45, 8-position, 8-wire black industrial bulkhead connector with cover
<b>Electrical Noise Reduction and Space Saving</b>	
G2X2LG6EMI	2" x 2" PanelMax shielded wiring duct; 6'
SD2EMI	EMI noise shield kit for 2" height Panduit wiring duct; two 3' sections, four bonding clips, and anti-oxidizing paste
DRD22LG6	2" height PanelMax DIN rail wiring duct with dual wiring channels. Base, covers, and DIN rail fasteners included (DIN sold separately)
CWD2LG6	One-piece corner wiring duct base for use with 2" height wiring duct.
<b>Grounding/Bonding &amp; Power</b>	
UGB2/0-414-12	Universal ground bar accepts #14 – #4 AWG wire in 12-wire ports and up to a 2/0 AWG main equipment grounding conductor with a compression or mechanical connector
BS100445	Braided bonding strap, one-hole, insulated, 4.00" L x 1.06" W
F91-40-L	Ferrule, non-insulated, 4/0 AWG wire range
<b>Identification &amp; Safety</b>	
C120X150APT-22	Raised panel label, keyhole, 1.2" W x 1.5" H
R050X075V1T	Thermal transfer, vinyl, 0.50" W x 0.75" H
IAPNG5EWH	IndustrialNet GFCI data access port, Cat 5e

### For More Information

For more information, contact your local distributor, Panduit Sales Representative, or Rockwell Automation Sales Representative.  
[www.panduit.com/ia](http://www.panduit.com/ia)  
[iai@panduit.com](mailto:iai@panduit.com)

### About this Configuration

Control panels are being packed with more gear causing challenges with over crowding, susceptibility to noise, and challenging moves/adds/changes. This drawing lays out options to address these concerns.

#### Cable Protection and Management

Minimizing chaffing, cuts, and strains is paramount to achieve high reliability and designed performance. The key is securing, covering, and separating cables from hazards.

#### Electrical Noise Reduction and Space Savings

Mitigating electrical noise and utilizing 3D panel space facilitates higher density device designs to fit into tight panel layouts or lead to a smaller panel footprint.

#### Grounding & Bonding

Grounding and bonding is critical for reliable network communication, especially dissipating high frequency noise. Utilizing ground bars and bonding straps is a best practice for grounding.

#### Identification & Safety

Moves, adds, and changes need to be done correctly, efficiently, and safely. Identification is critical to guide personnel to make the right connections and prevent erroneous disconnects. Protect personnel by preventing contact with hazards while providing same capability.

#### Networking

Ethernet-enabled controls, drives, and sensing hardware are proliferating. Panels need to manage network cabling and devices while minimizing environmental impacts like heat, electrical noise, vibration, etc.

## Bill of Materials (cont.)

Part Number	Description
<b>Networking</b>	
FI2D204	OM2 4-fiber PCF multimode low smoke zero halogen riser rated indoor breakout cable
UTP28SP1	Cat 6, 28 AWG (small diameter) UTP patch cord with TX6 modular plugs
CDPP8RG FDME8RG	8-port DIN rail mount copper or fiber patch panel. Mounting latches securely attach unit to DIN rail
UPS003024024015	Uninterruptible Power Supply (UPS), 35 watts for 5 minutes, 24 VDC in/out, DIN rail mount
FSPD504	OM2 4-fiber dielectric conduited, LSZH-riser rated, multimode indoor distribution cable for backbones
PSM7004BU-KD	Cat 7, LSZH, 4-pair, stranded, S/FTP shielded marine copper cable, oil- and fuel-resistant